

532nm, λ/4 Polymer Waveplate



Polymer Waveplates (Retarders)

Stock #90-939 ☐ In Stock



1



C\$603.40

ADD TO CART

Qty 1-5

C\$603.40

Qty 6+

C\$483.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Coating:

R_{avg} <0.5% @ 400 - 700nm

Design Wavelength DWL (nm):

532

Diameter (mm):

25.00

Substrate: ☐

[B270](#)

Retardance:

$\lambda/4$

Thickness (mm):

2.00

Thickness Tolerance (mm):

± 0.2

Type:

Polymer Waveplate

Parallelism (arcmin):

3.00

Dimensional Tolerance (mm):

+0.0/-0.2

Construction:

Birefringent Polymer Stack

Retardance Tolerance (nm):

± 10 @ 532

Retardance Order:

0

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Reach 224:

[Compliant](#)

Certificate of Conformance:

[View](#)