

#55, 8" x 10", 50 Sheets, Adhesive Back Flock Paper



Light Absorbing Black-Out Material (Adhesive Backing)

Stock **#54-579** [CONTACT US](#)

-

1

+

C\$368²⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$368.20 each
Need More?	Request Quote

Product Downloads

General	
50.00	Number of Sheets:
Note: Minimum application temperature for adhesive is +40°F	
Physical & Mechanical Properties	
8 x 10	Dimensions (inches):
0.02	Thickness (inches):

Environmental & Durability Factors	
-65 to +165	Operating Temperature (°F):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 251:

Product Details

- For Light Trapping, Baffling, Beam Stopping
- Light Absorbing Black-Out Material is a velvet-like, adhesive, or non-adhesive backing that allows black-out material to be applied to any acceptable surface. Flocked material surface characteristics are consistent across product lines, but higher paper numbers indicate thicker, more durable levels of backing for the material. The #40 backing is paper-thin (0.01" thick), the #55 adhesive backing is thicker (0.02" thick) but still very flexible, and the #65 backing has a texture similar to heavy construction paper (0.02" thick). Light Absorbing Black-Out Material that utilizes a non-adhesive backing will have a slightly duller (less reflective) finish than the adhesive-backed flock material. This material is optimal for light trapping, baffling, and beam stopping.
- Note:** This material is meant to absorb light and is not recommended for direct exposure to high-power lasers.