

42mm Max. Aperture, Iris Diaphragm



Stock **#30-118** ☐ In Stock

-

1

+

C\$130.20

ADD TO CART

Qty 1-4
C\$130.20
Qty 5+
C\$115.36
Volume Pricing
Request Quote

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
2

Maximum Aperture (mm):
42.0

Outer Diameter (mm):
58.0

Construction: Brass Housing, Blue Tempered Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 12.70
Number of Leaves: 18.00
Thickness (mm): 6.50

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)