


TECHSPEC® 5mm 30R/70T Cube Beamsplitter



Stock **#68-545** ☐ In Stock

-

1

+

C\$250.60

ADD TO CART

Qty 1-5
C\$250.60
Qty 6+
C\$200.20
Volume Pricing
Request Quote

Get Product Downloads



Beam Deviation (arcmin):
±3

Bevel:
Protective bevel as needed

Coating:
λ/4 MgF₂ @ 550nm on Faces
Multilayer Dielectric on Hypotenuse

Construction: Cube
Dimensions (mm): 5.0 x 5.0 x 5.0 ±0.10
Reflection/Transmission Ratio (R/T): 30/70
Reflection/Transmission Tolerance (%): ±5
Substrate: ☐ N-BK7
Surface Flatness (P-V): λ/4
Surface Quality: 60-40
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View