


TECHSPEC® 5mm Aperture, 60mm L Standard NA, Hexagonal Light Pipe



N-BK7 Light Pipe Homogenizing Rods



Stock **#48-583** ☐ In Stock

1 **C\$168.00**

ADD TO CART

Qty 1-5
C\$168.00
Qty 6+
C\$134.40
Volume Pricing
Request Quote

Get Product Downloads



Coating:
Uncoated

Substrate: ☐
[N-BK7](#)

Length (mm): 60.00
Surface Quality: 60-40
Type: Light Pipe
Entrance and Exit Aperture (mm): 5.00
Parallelism (arcmin): 5.00
Length Tolerance (mm): ±0.3
Aperture Tolerance (mm): ±0.10
Image Orientation: Light Homogenization
Light Source NA: Standard
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): 1λ

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View