

5mm FL Wide Angle Low Distortion Lens



#68-670

Stock **#68-670** ☒ In Stock

1

C\$1,113.00

ADD TO CART

Qty 1+
C\$1,113.00
Volume Pricing
Request Quote

Get Product Downloads

Field of View @ Min Working Distance (mm):
200.00

Iris Option:
Fixed

Length (mm):
38.20

Horizontal Field of View, 1/2" Sensor:
65.2°

Horizontal Field of View, 2/3" Sensor:
82.4°

Filter Thread: M40.5 x0.50
Maximum Diameter (mm): 42.0
Weight (g): 75.00
Maximum Image Circle (mm): 11.00
Type: Fixed Focal Length Lens
Focal Length FL (mm): 5.00
Maximum Sensor Format: 2/3"
Working Distance (mm): 150 - ∞
Mount: C-Mount
Aperture (f/#): f/2.8
Distortion (%): <0.5
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View