

[See all 21 Products in Family](#)

## TECHSPEC® 5mm M40 Spacer Tube



5mm M40 Spacer Tube



Stock #70-704 **20+ In Stock**

1  C\$53<sup>20</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	C\$53.20 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

**Note:**  
Extensions Tube with Male/Female M40 Threads

**Type:**  
Spacer Tube

**Compatible Lens:**  
[#29-261](#)

#### Physical & Mechanical Properties

5.00 Tube Length (mm):

Brass Construction:

---

## Regulatory Compliance

[View](#) Certificate of Conformance:

---

## Product Details

- APS-C (27.9mm), TFL-Mount Lens or M40 Mount Lens
- Greater than 30 MegaPixels, 3.45µm Pixel Size Sensors
- High Resolution, Compact APS-C Lens (CA)
- 35mm to 100mm Focal Length

TECHSPEC® CA (Compact APS) Series Fixed Focal Length Lenses are designed for high-resolution large-format sensors. Covering the APS-C format sensors with a 28mm image circle, these lenses feature a [TFL Mount](#) or M40 Mount. TFL Mounts feature an M35 x 0.75 thread with a 17.5mm flange distance, and offer the same robustness and ease of use as a C-Mount. M40 Mounts feature a M52 x 0.75 thread with a 17.526mm flange and provide a robust, large-format mounting solution ideal for high-resolution and larger image sensors with improved mechanical stability and optical performance compared to smaller format mounts. TECHSPEC® CA Series Fixed Focal Length Lenses offer a compact size while accommodating large format sensors, making them ideal for machine vision and [factory automation](#) applications.

These lenses won the [3rd place 2020 Inspect Award](#) and the [Silver-Level 2020 VSD Innovators Award](#).

---