

TECHSPEC® 5mm, Uncoated, N-BK7 Right Angle Prism



N-BK7 Right Angle Prisms

Stock #32-328 ☐ In Stock

-

1

+

C\$64.40

ADD TO CART

Qty 1-5

C\$64.40

Qty 6+

C\$57.96

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:
Uncoated

Substrate: ☐
[N-BK7](#)

Surface Quality:
60-40

Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.1
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 7.10
Length of Legs (mm): 5.00
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View