

TECHSPEC® 5mm VIS-EXT, 50R/50T, Non-Polarizing Cube Beamsplitter



Stock **#11-287** ☐ In Stock

1 **C\$289.80**

ADD TO CART

Qty 1-5
C\$289.80
Qty 6+
C\$229.60
Volume Pricing
Request Quote

Get Product Downloads



Beam Deviation (arcmin):
≤2

Bevel:
Protective bevel as needed

Clear Aperture (%):
>90

Coating:

MS-EXT (400-640nm)
Coating Specification: R _{avg} <0.5% @ 400 - 640nm
Construction: Cube
Dimensions (mm): 5.0 x 5.0 x 5.0 ±0.1
Reflection/Transmission Ratio (R/T): 50/50
Substrate:  N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Wavelength Range (nm): 400 - 640
 Ts-Tp : <6%
Absolute Transmission (%): 45 ±10

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View