

5mW, 635nm Laser Bat Power ZAT, 60° X-Hair (Recertified 05-P)

Stock #19-540-RCD-05P **RECERTIFIED** 1 In Stock



1 C\$417^{.20}



ADD TO CART

Volume Pricing	
Qty 1+	C\$417.20 each
Need More?	Request Quote



General	
Style: Crosshair	Laser Class - CDRH: 1M
Physical & Mechanical Properties	
Weight (g): 162	Length (mm): 124.00
Optical Properties	
Wavelength (nm): 635.00	Color: Red
Fan Angle (°): 60.00	Focus Range (mm): Up to 1,500mm
Electrical	
Output Power (mW): 5	
Hardware & Interface Connectivity	
Power Requirement: 1 AA Battery (Not Included)	Output Type: Free Space
Environmental & Durability Factors	
Environmental Rating: IP40	
Regulatory Compliance	
Certificate of Conformance: View	

Product Details

- Bright Red 635nm Wavelength
- Line, Crosshair, or Dot Projection
- Battery Powered Operation with a Fixed Focus
- Sturdy, Metal Housing

Z-Laser ZAT Battery Powered Lasers are ideal for positioning and alignment applications. Their battery powered design provides maneuverability by removing the need for a fixed power supply. IP40 rated, shock proof, and vibration proof with a sturdy, metal housing makes these lasers excellent for harsh environments and repeated use. Z-Laser ZAT Battery Powered

Related Products



Laser Alignment Glasses



Laser Safety Glasses and Goggles



Red and IR Alignment Laser Diodes



Z-Laser Green Focusable Diode Modules

Resources

Media Type

- Technical Tool
- Application Note
- Video
- FAQ
- Glossary
- Published Article
- Scientific Paper

TECHNICAL TOOL

Gaussian Beams Calculator

APPLICATION NOTE

Gaussian Beam Propagation

APPLICATION NOTE

Common Laser Types

VIDEO

Understanding Lasers and How They're Used Every...

FAQ

Can a laser beam be seen from the side?

FAQ

What factors are involved in how well I can see a laser...

[View More](#)