


[See all 6 Products in Family](#)

5mW, 635nm Laser Bat Power ZAT



Stock **#19-444** 1 In Stock

-

1

+

C\$400⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-9	C\$400.40 each
Qty 10+	C\$359.80 each
Need More?	Request Quote

Product Downloads		
General		
Elliptical Dot	Style:	
3R	Laser Class - CDRH:	
Physical & Mechanical Properties		
162	Weight (g):	
124.00	Length (mm):	
Optical Properties		
635.00	Wavelength (nm):	
Red	Color:	
Up to 2,000mm	Focus Range (mm):	
Electrical		
5	Output Power (mW):	
Hardware & Interface Connectivity		
1 AA Battery (Not Included)	Power Requirement:	
Free Space	Output Type:	
Environmental & Durability Factors		
IP40	Environmental Rating:	
Regulatory Compliance		
View	Certificate of Conformance:	

Product Details

- Bright Red 635nm Wavelength
- Line, Crosshair, or Dot Projection
- Battery Powered Operation with a Fixed Focus
- Sturdy, Metal Housing

Z-Laser ZAT Battery Powered Lasers are ideal for positioning and alignment applications. Their battery powered design provides maneuverability by removing the need for a fixed power supply. IP40 rated, shock proof, and vibration proof with a sturdy, metal housing makes these lasers excellent for harsh environments and repeated use. Z-Laser ZAT Battery Powered Lasers are suitable for use in industrial environments such as Automotive, Paper, Wood, Ceramic, and Metal. Available with 1 or 5mW output powers, the lasers utilize one AA battery (not included) ensuring easy maintenance and an extended lifetime.