

TECHSPEC® 6" Diameter x 36" FL Protected Gold, Parabolic Mirror



Stock **#32-071-566** [CONTACT US](#)

- 1 + **C\$1,198.40**

ADD TO CART

Qty 1-4
C\$1,198.40
Qty 5+
C\$1,019.20
Volume Pricing
Request Quote

Get Product Downloads

Substrate: [BOROFLOAT®](#)

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 6.0 +0.06/-0
Diameter (mm): 152.40 +1.5/-0
Effective Focal Length EFL (inches): 36.0
Effective Focal Length EFL (mm): 914.40
Radius of Curvature (mm): 1,828.80
Aperture (f/#): f/6
Coating: Protected Gold (700-10000nm)
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 138
Edge Thickness ET (inches): 1.00
Edge Thickness ET (mm): 25.40
Type: Parabolic Mirror
Wavelength Range (μm): 0.7 - 10
Wavelength Range (nm): 700 - 10000
Damage Threshold, Reference: ☐ 0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant