

152.4mm/6.0" Optic Dia., Optical Cell Kinematic Mount



Stock #36-474 ☒ In Stock

1 **C\$2,207.80**

ADD TO CART

Qty 1-4
C\$2,207.80
Qty 5+
C\$2,097.76
Volume Pricing
Request Quote

Get Product Downloads

Type:
Adjustable - Tip-Tilt

Type of Optics:
Circular

Size of Compatible Optics (mm):
152.4

Clear Aperture CA (inches): 5.75
Clear Aperture CA (mm): 146.1
Optical Centerline (mm): 114.3
Range: 5°
Dimensions (inches): 8.00 x 6.00 x 8.00
Dimensions (mm): 203.2 x 152.4 x 203.2
Weight (lbs): 7.5
Inner Diameter (inches): 6.187 x 32 TPI
Construction: Black Anodized Aluminum, Stainless Steel
Diameter of Compatible Optics (inches): 6.00
Optical Centerline (inches): 4.50
Optic Holding Style: Retaining Ring
Max. Thickness of Compatible Optics (mm): 27.0
Adjustment Screw Pitch (inches): 0.015

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View