

60mm Dia. x 39.8mm FL, Aspheric Condenser Lens



Stock **#22-846** ☐ In Stock
[Other Coating Options](#)

-

1

+

C\$127.40

ADD TO CART

Qty 1-10
C\$127.40
Qty 11+
C\$112.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm): 60.00 +0.0/-0.2
Effective Focal Length EFL (mm): 39.80
Numerical Aperture NA: 0.76
Back Focal Length BFL (mm):

25.58
Substrate: H-K51
Focal Length Tolerance (%) : ±8
Coating: Uncoated
Centering (arcmin): ≤30
Surface Quality: 80-50 (typical)
Clear Aperture CA (mm): 54.00
Edge Thickness ET (mm): 2.16
Center Thickness CT (mm): 26.00 ±0.30
f/#: 0.66
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 60.00
Radius R₂ (mm): 80.00
Shape of Back Surface: Convex
Type: Condenser Lens
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View