

TECHSPEC® 6.0mm Dia. x 9.0mm FL, VIS-EXT, Inked, Plano-Convex Lens



Stock **#88-639-INK** 3-5 DAYS

[Other Coating Options](#)

- 1 +

C\$70.70

ADD TO CART

Qty 1-9
C\$70.70
Qty 10+
C\$63.70
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.00 ±0.025

Effective Focal Length EFL (mm):
9.00 @ 587.6nm

Back Focal Length BFL (mm): 7.95
Coating: VIS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-SF5
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.75 ±0.05
Edge Thickness ET (mm): 0.95
Radius R₁ (mm): 6.05
Clear Aperture CA (mm): 5.4
f/#: 1.5
Numerical Aperture NA: 0.33
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 700
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View