

40mm Max. Aperture, Iris Diaphragm



Stock **#36-624** ☐ In Stock

-

1

+

C\$165.20

ADD TO CART

Qty 1-4
C\$165.20
Qty 5+
C\$146.16
Volume Pricing
Request Quote

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
2.5

Maximum Aperture (mm):
40.0

Outer Diameter (mm):
60.0

Construction: Aluminum Housing, Blue Tempered Spring Steel Leaves
Lever Diameter (mm): 7.00
Lever Length (mm): 13.00
Number of Leaves: 12.00
Thickness (mm): 7.80

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant