

60X Nikon Achromatic Finite Conjugate Objective

See More by [Nikon](#)



60X Nikon Achromatic Finite Conjugate Objective

Stock **#59-937** ☐ In Stock

-

1

+

C\$327.60

ADD TO CART

Qty 1+

C\$327.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Compatible Cover Glass Thickness (mm):
0.17

Effective Focal Length EFL (mm):
2.87

Field of View (mm):
0.30

Model Number:
MSB50600

Magnification:

60X
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.80
Mounting Threads: RMS / 20.32mm x 36 TPI
Type: Achromatic, Spring Loaded Head
Resolving Power (μm): 0.3
Depth of Field (μm): 0.30
Working Distance (mm): 0.24
Style: Finite Conjugate
Manufacturer: Nikon
Field Number (mm): 18
Immersion Liquid: N/A

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View