

TECHSPEC® 6.25mm Dia x -12.5mm FL Uncoated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock **#46-192** ☐ In Stock

1 **C\$83.30**

ADD TO CART

Qty 1-5

C\$83.30

Qty 6+

C\$66.50

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
6.25 +0.0/-0.2

Effective Focal Length EFL (mm):
-12.50

Substrate: ☐
[N-BK7](#)

f/#: 2.00
Numerical Aperture NA: 0.25
Coating: Uncoated
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): -13.16
Center Thickness CT (mm): 1.00
Center Thickness Tolerance (mm): ±0.1
Edge Thickness ET (mm): 1.80
Focal Length Tolerance (%): ±3
Radius R ₁ (mm): -6.48
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View