

63.5mm Clear Aperture, 2 Arcsec, Gold Retroreflector



Stock **#46-188** ☒ In Stock

- 1 + **C\$2,044.00**

ADD TO CART

Qty 1+
C\$2,044.00

Volume Pricing
Request Quote

Get Product Downloads

Beam Deviation (arcsec): 2.00
Clear Aperture CA (mm): 63.5
Coating: Protected Gold (700-2000nm)
Diameter (mm): 89.40
Exiting Wavefront Accuracy: 0.6λ

Substrate:  BOROFLOAT®

Surface Quality:
80-50

Mounting Threads:
(6) ¼-20, (5) M6 x 1.0

Type:
Retroreflector

Dimensional Tolerance (mm):
±1.6

Image Orientation:
Left-Handed

Ray Deviation (°):
180

Wavelength Range (nm):
700 - 2000

Regulatory Compliance

RoHS 2015:
[Compliant](#)

REACH 201:
[Compliant](#)

Certificate of Conformance:
[View](#)