

63.5mm Clear Aperture, 5 Arcsec, Aluminum Retroreflector



Stock **#46-178** ☐ In Stock

- 1 + **C\$1,680.00**

ADD TO CART

Qty 1+
C\$1,680.00

Volume Pricing
Request Quote

Get Product Downloads

Beam Deviation (arcsec):
5.00

Clear Aperture CA (mm):
63.5

Coating:
Enhanced Aluminum (450-650nm)

Diameter (mm):
89.40

Exiting Wavefront Accuracy:
1.5λ

Substrate:  BOROFLOAT®

Surface Quality:
80-50

Mounting Threads:
(6) ¼-20, (5) M6 x 1.0

Type:
Retroreflector

Dimensional Tolerance (mm):
±1.6

Image Orientation:
Left-Handed

Ray Deviation (°):
180

Wavelength Range (nm):
400 - 700

Regulatory Compliance

RoHS 2015:
[Compliant](#)

REACH 201:
[Compliant](#)

Certificate of Conformance:
[View](#)