


650nm, 25mm Dia., OD 2.0 Shortpass Filter



OD 2.0 Shortpass Filters

Stock **#15-260** ☐ In Stock

-

1

+

C\$145.60

ADD TO CART

Qty 1-9
C\$145.60
Qty 10+
C\$131.04
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.20

Angle of Incidence (°):
0

Optical Density OD (Average):
≥2.0

Cut-Off Wavelength (nm): 650.00 ±13
Substrate:  BOROFLOAT®
Coating: Hard Coated
Rejection Wavelength (nm): 675 - 850
Surface Quality: 60-40
Thickness (mm): 2.00 ±0.10
Transmission (%): ≥85
Transmission Wavelength (nm): 400 - 630
Type: Shortpass Filter
Clear Aperture (%): 90
Environmental Durability: ML-STD-810F, Section 507.4
Physical Durability: ML-C-48497A Section 3.4.1
Wavelength Range (nm): 400 - 850

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View