

6.5mm Diameter x 6mm FL, MgF₂ Coated, PCX Condenser Lens



Stock **#15-527** ☐ In Stock

[Other Coating Options](#)



1



C\$49.00

ADD TO CART

Qty 1-10

C\$49.00

Qty 11+

C\$44.80

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
6.50

Effective Focal Length EFL (mm):
6.00

Numerical Aperture NA:
0.58

Substrate: ☐

Float Glass
Focal Length Tolerance (%): ±7
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Surface Quality: 80-50 (typical)
Center Thickness CT (mm): 3.40 ±0.2
f/#: 0.86
Bevel: Protective bevel as needed
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 400 - 700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant