

TECHSPEC® 675nm 12.5mm Diameter, OD 2.0 Shortpass Filter



TECHSPEC OD 2.0 Shortpass Filters

Stock **#64-597** ☐ In Stock

-

1

+

C\$133.00

ADD TO CART

Qty 1-5

C\$133.00

Qty 6+

C\$113.12

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.2

Angle of Incidence (°):
0

Optical Density OD (Average):
≥2.0

Cut-Off Wavelength (nm): 675.00
Substrate:  Fused Silica (Coming 7980)
Coating: Traditional Coated
Rejection Wavelength (nm): 700 - 875
Surface Quality: 40-20
Thickness (mm): 1.50
Thickness Tolerance (mm): ±0.1
Transmission (%): >85
Transmission Wavelength (nm): 400 - 655
Type: Shortpass Filter
Clear Aperture (%): 80.00
Transmitted Wavefront, P-V: λ/4
Slope Factor (%): ±3
Cut-Off Tolerance (%): ±2
Wavelength Range (nm): 400 - 875

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View