

TECHSPEC® 6mm Dia x 24mm FL NIR I Coated, Illumination Grade PCX Cylinder Lens



Stock **#69-742** ☐ In Stock

-

1

+

C\$111.30

ADD TO CART

Qty 1-5
C\$111.30
Qty 6+
C\$88.90
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.00

Effective Focal Length EFL (mm):
24.00

Substrate: ☐
[N-BK7](#)

f/#:

Numerical Aperture NA: 0.13
Coating: NIR I (600-1050nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 600 - 1050
Back Focal Length BFL (mm): 22.94
Center Thickness CT (mm): 1.60
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.23
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 12.40
Surface Quality: 60-40
Damage Threshold, By Design: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View