

6mm Dia. x 6mm FL, Commercial Grade, Double-Convex Lens



Stock **#27-722** CLEARANCE ☐ In Stock

- 1 +

C\$20.93

ADD TO CART

Qty 1+
C\$20.93

Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
6.00 +0.00/-0.10

Back Focal Length BFL (mm):
5.00

Effective Focal Length EFL (mm):
6.00

Coating:
Uncoated

Substrate: ☐
N-SK18

Centering (arcmin): 6.00
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 1.65
Radius R ₁ (mm): 7.02
Clear Aperture CA (mm): ≥5.1
f#: 1.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.5
Type: Double-Convex Lens
Wavelength Range (μm): 0.38 - 2.2

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View