

TECHSPEC[®] 6mm Dia. x -9mm FL, VIS-NIR, Inked, Double-Concave Lens



Stock #48-941-INK [CONTACT US](#)

-

1

+

C\$71.40

ADD TO CART

Qty 1-9

C\$71.40

Qty 10+

C\$64.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):

6.00

Effective Focal Length EFL (mm):

-9.00

Substrate: N-BK7
f/#: 1.5
Numerical Aperture NA: 0.33
Coating: VIS-NIR (400-1000nm)
Type: Double-Concave Lens
Wavelength Range (nm): 400 - 1000
Back Focal Length BFL (mm): -9.32
Bevel: Protective bevel as needed
Center Thickness CT (mm): 1.00
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <3
Clear Aperture CA (mm): 5.4
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Edge Thickness ET (mm): 1.79
Focal Length Tolerance (%): ±1
Radius R₁=R₂ (mm): -9.47
Surface Quality: 40-20

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View