

## 6mm FL Compact Fixed Focal Length Lens



Fixed Focal Length Lenses

Stock **#68-674** ☐ In Stock

[Similar Products](#)

1  **C\$595.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1+                        |
| C\$595.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

### Get Product Downloads

Field of View @ Min Working Distance (mm):  
174.00

Iris Option:  
Variable

Length (mm):  
34.00

Horizontal Field of View, 1/2" Sensor:  
57.3°

Filter Thread:

|                                             |
|---------------------------------------------|
| M25.5 x0.50                                 |
| <b>Maximum Diameter (mm):</b><br>31.0       |
| <b>Weight (g):</b><br>60.00                 |
| <b>Maximum Rear Protrusion (mm):</b><br>8.1 |
| <b>Maximum Image Circle (mm):</b><br>8.00   |
| <b>Type:</b><br>Fixed Focal Length Lens     |
| <b>Focal Length FL (mm):</b><br>6.00        |
| <b>Maximum Sensor Format:</b><br>1/2"       |
| <b>Working Distance (mm):</b><br>200 - ∞    |
| <b>Mount:</b><br>C-Mount                    |
| <b>Aperture (f/#):</b><br>f/1.4 - f/16      |
| <b>Lens Wavelength Range:</b><br>VIS        |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Exempt</a>                |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Contains SVHC(s)</a>      |