

6" Kinematic Mount



#53-039 6" Kinematic Mount

Stock **#53-039** **3 In Stock**

⊖ 1 ⊕ C\$805⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	C\$805.00 each
Qty 5-9	C\$710.78 each
Qty 10-25	C\$654.78 each
Need More?	Request Quote

Product Downloads

General

Adjustable - Tip-Tilt **Type:**

Physical & Mechanical Properties

2.66 **Weight (lbs):**

Black Anodized Aluminum **Construction:**

±4.0

Fine Tilt Angle (°):

Regulatory Compliance

Compliant

RoHS 2015:

View

Certificate of Conformance:

Compliant

Reach 235:

Product Details

- Stand Alone Jaw Clamp Mounts (8-32 Mounting) or with Kinematic Frame
- Accepts up to 4-1/4" Diameters
- Fine Angular Resolution Kinematic

An affordable self-centering jaw clamp for use with components up to 4-1/4" Dia. Mounted alone on the 8-32 tapped hole in the base, or to the 6" kinematic frame, the jaw clamp precisely centers your components without the danger of warping them with clumsy edge clips. The kinematic mount has an angled base, to allow fastening by either 1/4-20 cap screws or un-fastened for stand-alone use. Locking screw allows jaw position to be fixed to secure against accidental movement. Mount features precise kinematic pivot movement (two-axis tilt) with orthogonal three-point suspension. Adjustment is made by three 64 pitch screws. Construction is black anodized aluminum.

Technical Information

