

TECHSPEC® 70mm, 150mm Radius, English Goniometer



TECHSPEC® Goniometers



Stock #66-533 [CONTACT US](#)

- 1 +

C\$978.60

ADD TO CART

Qty 1-2

C\$978.60

Qty 3+

C\$852.46

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:  
Goniometer

Type of Drive:  
Lead Screw

Type:

|                                                          |
|----------------------------------------------------------|
| English                                                  |
| <b>Stage Size (mm):</b><br>70 x 70                       |
| <b>Travel (°):</b><br>±10                                |
| <b>Construction:</b><br>Aluminium Stage                  |
| <b>Leadscrew Pitch (mm):</b><br>0.5                      |
| <b>Load Capacity (kg):</b><br>6                          |
| <b>Mounting Threads:</b><br>(9) ¼-20, (4) 6-32, (8) 2-56 |
| <b>Radius R (mm):</b><br>150                             |
| <b>Resolution (arcmin):</b><br>5                         |
| <b>Stage Size (inches):</b><br>2.75 x 2.75               |
| <b>Weight (kg):</b><br>0.3                               |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |