

50mm Max. Aperture, Iris Diaphragm



Stock **#32-617** ☐ In Stock

-

1

+

C\$189.00

ADD TO CART

Qty 1-4
C\$189.00
Qty 5+
C\$167.44
Volume Pricing
Request Quote

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
2.5

Maximum Aperture (mm):
50.0

Outer Diameter (mm):
70.0

Construction: Brass Housing, Blue Tempered Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 15.00
Number of Leaves: 16.00
Thickness (mm): 7.50

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)