

[All Products](#) / [Optics](#) / [Fiber Optics](#) / [Fiber Optic Tapers and Faceplates](#)

[See all 10 Products in Family](#)

Fiber Optic Faceplate, 75 x 50 x 3mm



Fiber Optic Faceplates

Stock **#55-142** [CONTACT US](#)

⊖ 1 ⊕

C\$1,650.60

ADD TO CART

Qty 1-4
C\$1,650.60
Qty 5+
C\$1,455.02
Volume Pricing
Request Quote

Get Product Downloads

Distortion (%): 1.00
Substrate: Schott 47A Glass with EMA
Numerical Aperture NA: 1.00
Operating Temperature (°C):

-10 to +300
Resolution: 102 lp/mm
Dimensions (mm): 75 x 50 x 3
Surface Quality: 80-50
Thickness Tolerance (mm): ±0.1
Resolving Power (µm): 6.00
Dimensional Tolerance (mm): ±0.2
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 6.8
Core/ Clad Ratio: 75 / 25

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
