

TECHSPEC® 75mm, Enhanced Aluminum Coated, N-BK7 90° Specialty Mirror



Stock **#47-309** ☐ In Stock

-

1

+

C\$637.00

ADD TO CART

Qty 1-5
C\$637.00
Qty 6+
C\$509.60
Volume Pricing
Request Quote

Get Product Downloads



Clear Aperture CA (mm):
73.5

Coating:
Enhanced Aluminum (450-650nm)

Substrate: ☐
[N-BK7](#)

Surface Quality:

40-20
Type: Right Angle Mirror
Dimensional Tolerance (mm): ±0.1
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Clear Aperture (%): 90.00
Length of Hypotenuse (mm): 106.10
Length of Legs (mm): 75.00
Coating Specification: R _{avg} >95% @ 450 - 650nm
Wavelength Range (nm): 450 - 650
Surface Flatness (P-V): λ/4
Coating Type: Metal
Damage Threshold, Reference: ☐ 0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
