

59mm Max. Aperture, Iris Diaphragm



Stock **#32-616** [CONTACT US](#)

- 1 + **C\$264.60**

ADD TO CART

Qty 1-4
C\$264.60
Qty 5+
C\$234.22
Volume Pricing
Request Quote

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
7.0

Maximum Aperture (mm):
59.0

Outer Diameter (mm):
77.0

Construction: Brass Housing, Blue Tempered Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 14.80
Number of Leaves: 20.00
Thickness (mm): 8.00

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)