

78mm Standard UV Fixed Focal Length Lens



78mm Standard UV Fixed Focal Length Lens, #57-543

Stock **#57-543** [CONTACT US](#)

⊖ 1 ⊕ **C\$6,230.00**

ADD TO CART

Qty 1+
C\$6,230.00
Volume Pricing
Request Quote

Get Product Downloads

Field of View @ Min Working Distance (mm):
36.1

Iris Option:
Variable

Length (mm):
109.30

Horizontal Field of View, 1/2" Sensor:
36.1mm - 4.4°

Filter Thread:
M49.0 x0.75

Maximum Diameter (mm): 62.5
Weight (g): 446.00
Maximum Image Circle (mm): 16.00
Note: C-Mount adapter can be removed for use with M42 x 75 (T2-Mount) cameras
Type: Fixed Focal Length Lens
Focal Length FL (mm): 78.00
Maximum Sensor Format: 1"
Working Distance (mm): 440 - ∞
Mount: C-Mount
Aperture (f/#): f/3.8 - f/16
Lens Wavelength Range: UV-NIR

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View