

## 80 lp/mm, 1" x 3", Float Glass, Ronchi Ruling



Stock #38-261 CLEARANCE 2 In Stock

⊖ 1 ⊕ C\$336<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-4	C\$336.00 each
Qty 5+	C\$320.32 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### Physical & Mechanical Properties

Length (inches):  
3.00

Pattern Size (mm):  
12.7 x 25.4

Thickness (mm):  
1.10

Width (inches):  
1.00

### Optical Properties

---

Vacuum Deposited Chrome **Coating:**

80.00 **Frequency (lp/mm):**

---

Float Glass **Substrate:**

3.00 **Optical Density OD (Average):**

---

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

---

[Compliant](#) **Reach 240:**

---

## Product Details

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
- Ideal for Reticle and Field Calibration Requirements
- Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).

Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.

---