

## 80 lp/mm 1" x 3", Opal Glass Ronchi Ruling Slide



Stock **#59-548** **4 In Stock**

C\$459<sup>.20</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	C\$459.20 each
Qty 5+	C\$437.22 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Pattern Location is Centered **Note:**

No **NIST Certification:**

#### Physical & Mechanical Properties

±0.100 **Dimensional Tolerance (inches):**

25.40 **Length (mm):**

12.7 x 25.4

Pattern Size (mm):

1.52 ±0.100

Thickness (mm):

76.20

Width (mm):

±0.001

Line Width Tolerance (µm):

## Optical Properties

Vacuum Deposited Chrome

Coating:

80.00

Frequency (lp/mm):

Opal Glass

Substrate: □

>3.0

Optical Density OD (Average):

40-20

Surface Quality:

## Regulatory Compliance

Compliant

RoHS 2015:

[View](#)

Certificate of Conformance:

Compliant

Reach 235:

## Product Details

Opal Glass material has been discontinued by the manufacturer and may be available in limited quantities. [Contact us](#) for more information.

- Chrome on Opal
- Test Resolution of Reflective Systems
- High Tolerance