

808nm, 5mW, 500mA, SMA Connector, Fiber-Coupled LED



Fiber Coupled LEDs

Stock **#23-740** ☐ In Stock

-

1

+

C\$1,190.00

ADD TO CART

Qty 1+

C\$1,190.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Color:
Infrared

Connector:
SMA

Current (mA):
500 (maximum)

Operating Lifetime (hours):
~10,000

Output Power (mW):
5 (typical, with ø600µm Core Fiber)

Wavelength (nm): 808.00 (Nominal)
Contents of Kit: 1 x Mounted LED 1 x LED Driver 1 x SMA Cable for Modulation 1 x ø600µm, 1m Length, 0.22NA, MM Patchcord
Note: 5VDC Power Supply sold separately
Bandwidth (nm): 25 (FWHM)
Forward Voltage (V) : 3.6

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant