

60mm Max. Aperture, Iris Diaphragm



Stock **#36-625** ☐ In Stock

-

1

+

C\$275.80

ADD TO CART

Qty 1-4

C\$275.80

Qty 5+

C\$243.04

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
4.0

Maximum Aperture (mm):
60.0

Outer Diameter (mm):
82.0

Construction:
Aluminum Housing, Blue Tempered Spring Steel
Leaves

Lever Diameter (mm):
8.0

Lever Length (mm):
11.00

Number of Leaves:
17

Thickness (mm):
10.10

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 240:
[Compliant](#)