

85 x 50mm English Base Plate



Stock **#58-998** 20+ In Stock

-

1

+

C\$48^{.30}

ADD TO CART

Volume Pricing	
Qty 1+	C\$48.30 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:

English

Physical & Mechanical Properties

Length (mm):

85.00

50.00	Width (mm):
7.00	Thickness (mm):
Black Anodized Aluminum	Construction:
6	Number of Slots:

Threading & Mounting

(4) 8-32, (5) 1/4-20	Mounting Threads:
----------------------	-------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

PRODUCT DETAILS

- Two Size Options
 - Two Platform Options: English or Metric
 - English: Four #8-32 holes on 1/2" Square and Four 1/4-20 Holes on 1" Square
 - Metric: Four M4 x 0.7 holes on 12.5mm Square and Four M6 x 1 Holes on 25mm Square
 - Anodized Aluminum Construction
- Base Plates have Metric or English threaded holes and additional center trapped hole (M6 x 1 or 1/4-20). Base Plates also have extended center slots that ensure full use on matching metric or English breadboard patterns. 85mm x 50mm Base Plates have same tapped holes and slots as 60mm x 35mm Base Plates, but with extra short slots for added flexibility.

TECHNICAL INFORMATION

