

## 8.5mm FL Ultra High Resolution Fixed Focal Length Lenses



#68-684



Stock **#68-682** ☐ In Stock

[Similar Products](#)

- 1 +

**C\$2,296.00**

ADD TO CART

Qty 1+

C\$2,296.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Field of View @ Min Working Distance (mm):  
96.5

Iris Option:  
Variable

Length (mm):  
56.00

Horizontal Field of View, 1/2" Sensor:

|                                            |
|--------------------------------------------|
| 96.5mm - 40.8°                             |
| <b>Filter Thread:</b><br>M34 x 0.50        |
| <b>Maximum Diameter (mm):</b><br>36.0      |
| <b>Weight (g):</b><br>115.00               |
| <b>Maximum Image Circle (mm):</b><br>11.00 |
| <b>Type:</b><br>Fixed Focal Length Lens    |
| <b>Focal Length FL (mm):</b><br>8.50       |
| <b>Maximum Sensor Format:</b><br>2/3"      |
| <b>Working Distance (mm):</b><br>100 - ∞   |
| <b>Mount:</b><br>C-Mount                   |
| <b>Aperture (f/#):</b><br>f/1.8 - f/22     |
| <b>Maximum Distortion (%):</b><br><0.31%   |
| <b>Lens Wavelength Range:</b><br>VIS       |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Exempt</a>                |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Contains SVHC(s)</a>      |