

8mm FL SWIR Series Fixed Focal Length Lens



Stock **#83-815** ☒ In Stock

1 **C\$2,947.00**

ADD TO CART

Qty 1+
C\$2,947.00

Volume Pricing
Request Quote

Get Product Downloads

Field of View @ Min Working Distance (mm): 165.00
Iris Option: Variable
Length (mm): 58.00
Filter Thread: M55.0 x0.75
Maximum Diameter (mm): 57.0

Weight (g): 205
Horizontal Field of View, 1" Sensor: 79.7°
Maximum Image Circle (mm): 16.00
Type: Fixed Focal Length Lens
Focal Length FL (mm): 8.00
Maximum Sensor Format: 1"
Working Distance (mm): 100 - ∞
Mount: C-Mount
Aperture (f/#): f/1.4 - f/16
Distortion (%): <-2.0
Lens Wavelength Range: SWIR

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)