


900nm, 12.5mm Dia., OD 2.0 Longpass Filter



OD 2.0 Longpass Filters

Stock **#15-220** ☐ In Stock

-

1

+

C\$114.80

ADD TO CART

Qty 1-9
C\$114.80
Qty 10+
C\$103.32
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50 +0.00/-0.20

Angle of Incidence (°):
0

Optical Density OD (Average):
≥2.0

Cut-On Wavelength (nm): 900.00 ±18
Substrate:  BOROFLOAT®
Coating: Hard Coated
Rejection Wavelength (nm): 600 - 860
Surface Quality: 60-40
Thickness (mm): 2.00 ±0.10
Transmission (%): ≥85
Transmission Wavelength (nm): 940 - 1600
Type: Longpass Filter
Clear Aperture (%): 90
Environmental Durability: ML-STD-810F, Section 507.4
Physical Durability: ML-C-48497A Section 3.4.1
Wavelength Range (nm): 600 - 1600

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View