

940nm, UltraSeal Washdown Spot Light

See More by [Advanced Illumination](#)



Advanced Illumination High Intensity UltraSeal Washdown Spot Lights

Stock **#21-975** CLEARANCE **1 In Stock**

-

1

+

C\$826^{.67}

~~C\$1,653.33~~

ADD TO CART

Volume Pricing	
Qty 1+	C\$1,653.33 C\$826.67 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

SPECIFICATIONS

General

SL316M-940IC

Model Number:

LED Lifetime (hours):

50,000	
	Number of LEDs:
25	
	Type of Illumination:
LED Illuminator	
	Manufacturer:
Advanced Illumination	
	Geometry:
Spot Light	
	Illumination Mode:
Constant	
Physical & Mechanical Properties	
	Weight (g):
290	
Optical Properties	
	Color:
IR	
	Wavelength (nm):
940.00	
Hardware & Interface Connectivity	
	Connector:
Flying Leads	
	Power Supply:
Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	
	Length of Cable (m):
2	
Environmental & Durability Factors	
	Operating Temperature (°C):
0 to +60	
Regulatory Compliance	
	Certificate of Conformance:
View	

PRODUCT DETAILS

- IP69K Certified for Extreme Washdown Environments
- Ideal for Hygienic and Aseptic Manufacturing Applications
- Intensity of Over 60,000 Lux at 300mm Working Distance

Advanced Illumination High Intensity UltraSeal Washdown Spot Lights are ideal for extreme environments including high pressure steam cleaning and prolonged liquid immersion. Available in five colors, these spot lights feature high intensity output and consistent uniformity. These spot lights are IP69K certified and their proprietary nickel finish ensures better thermal conductivity than stainless steel while the sealed design reduces the potential for material buildup and improves cleanability. Advanced Illumination High Intensity UltraSeal Washdown Spot Lights can be used in hygienic inspection environments, aseptic manufacturing, and food and beverage applications.