

TECHSPEC®

9mm Dia. x 27mm FL VIS-EXT, Inked, Double-Convex Lens



Stock **#89-139-INK** 3-5 DAYS

[Other Coating Options](#)

- 1 +

C\$74.20

ADD TO CART

Qty 1-9
C\$74.20
Qty 10+
C\$66.85
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
9.00 ±0.025

Back Focal Length BFL (mm):
26.08

Effective Focal Length EFL (mm):

27.00
Coating: VS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.74
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 2.00
Radius R₁=R₂ (mm): 27.43
Clear Aperture CA (mm): 8.1
f/#: 3.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.17
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View