

9X Metric Linear Scale & Comparator Set



Stock **#02-048** **3 In Stock**

C\$254⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	C\$254.80 each
Need More?	Request Quote

Product Downloads

General

Metric Reticle Type:

Kellner-type / AR coated Type of Optics:

Nylon case ([#36-286](#)) is sold separately. Note:

Physical & Mechanical Properties

0.75 **Field of View (inches):**

0.68 **Diameter of Included Lens (inches):**

27.00 **Diameter of Compatible Reticle (mm):**

1.25 **Height (inches):**

40.8 **Weight (g):**

Optical Properties

0.75 **Working Distance (inches):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Clear Base Admits Light
- High Power, Wide Field
- Reticle Included

Excellent for determining paper quality and ink absorption. Ideal for proofreaders. The transparent acrylic base rests directly on work for clear, close-up examinations. Base admits light to subject under view. 9X is Kellner-type, color-corrected, three-element lens system.

Twist focus with lock-ring for permanent setting. Contact reticle adapter ring on base accepts all 27mm diameter reticles.

Note: Nylon case ([#36-286](#)) is sold separately.

Reticle Description

Straight line scales for critical measurement in either English (inch) or metric. English/inch: 0 to 0.75" scale in 0.005" increments, numbered every 0.025 increments. Metric: 0 to 20mm scale in 0.1mm increments, numbered every 1.0mm.