

Pro 360 Digital Protractor, 0.1 Degree Resolution

See More by [Mitutoyo](#)



Stock **#78-356** NEW [CONTACT US](#)

- 1 + **C\$485²⁷**

ADD TO CART

Volume Pricing	
Qty 1+	C\$485.27 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General	
0 - 360°	Range:
950-317	Model Number:
Physical & Mechanical Properties	

0.1

Repeatability (°):

Regulatory Compliance

[View](#)

Certificate of Conformance:

PRODUCT DETAILS

- English and Metric Units
- Stainless Steel Construction
- High Measurement Resolution

Mitutoyo Pocket Rulers and Protractors are ideal tools for quick and accurate manual measurements in optical settings to maintain system performance. These Pocket Rulers feature a sliding stop for accurate measurements, are non-magnetic to prevent interference with sensitive applications, and feature a conversion chart on the back between inch divisions and millimeters. Protractors are available in four form factors to best match the application including digital, universal bevel, semi-circular base, and rectangular base. Mitutoyo Pocket Rulers and Protractors are made from stainless steel making them stronger than aluminum to maintain straightness and prevent distortion.