

[See all 3 Products in Family](#)

Achromatic Lens 6.25mm Dia. x 35mm FL, Uncoated



Stock **#32-306** CLEARANCE **7 In Stock**

- 1 + **C\$18^{.90}**

ADD TO CART

Volume Pricing	
Qty 1+	C\$18.90 each
Need More?	Request Quote

Product Downloads

#Max Edge Thickness of Curved Optic (mm):
3.8600000000

#Min Edge Thickness of Curved Optic (mm):
2.3600000000

General	
Achromatic Lens	Type:

Physical & Mechanical Properties	
2.30	Center Thickness CT 1 (mm):
	Center Thickness CT 2 (mm):

0.90	
6.2500000000 +0.00/-0.05	Diameter (mm):
2.86	Edge Thickness ET (mm):
±0.1	Center Thickness Tolerance (mm):
1.00	Centering (arcmin):
Optical Properties	
33.59	Back Focal Length BFL (mm):
Uncoated	Coating:
35.0000000000	Effective Focal Length EFL (mm):
N-BK7 / N-SF5	Substrate:
0.0800000000	Numerical Aperture NA:
23.1400000000	Radius R ₁ (mm):
-14.51	Radius R ₂ (mm):
-38.86	Radius R ₃ (mm):
40-20	Surface Quality:
±2	Focal Length Tolerance (%):
632.8	Focal Length Specification Wavelength (nm):
5.6	f/#:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Discounts up to 80% Off
- Quantities Extremely Limited
- Final Sale, No Returns

Shop the EO Mega Clearance presentations for the hottest deals on component-level products. Quickly browse the best optics, [imaging](#), and [photonics](#) deals you will ever see. Quantities are extremely limited and are sold on a first-come-first-serve basis.

Hurry, while supplies last. EO Mega Clearance products will never be sold again. Check out our standard [clearance products](#) for even more deals!

All products are final sale; EO will not accept returns. No additional information is available other than what is listed.

Compatible Mounts