


Adapter Plate for #55-029



#55-038



Stock **#55-038** 10 In Stock

-

1

+

C\$54^{.25}

ADD TO CART

Volume Pricing	
Qty 1-9	C\$54.25 each
Qty 10+	C\$48.72 each
Need More?	Request Quote

Product Downloads

General	
Adapter Brackets & Plates	Type:
Physical & Mechanical Properties	
2.36	Length (inches):
	Length (mm):

60.00	
	Dimensions (mm):
60 x 60 x 7	
Threading & Mounting	
	Mounting Threads:
(4) M4 x 0.7, (4) M3 x 0.5, (4) M2 x 0.4, (1) 1/4-20	
Regulatory Compliance	
	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 247:
Compliant	

Product Details

- Precision Micrometer Drive and Manual Drive Options
- 360° Coarse Rotation
- Micrometer Drive Models Provide ±5° Fine Rotation
- Black Anodized Aluminum Construction

Metric Rotary Stages feature slide-fit guide system, enabling 360° course rotation. Micrometer drive models feature a precision metric micrometer and a switchable clamp mechanism to change between course and fine movements for precise ±5° angular adjustment at any position. The manual drive model provides a smooth manual adjustment with 360° coarse movement, 1° increments. Metric Rotary Stages feature a locking mechanism to fix the stage position. For breadboard mounting, use the [Metric Base Plates](#).

Technical Information

