

[See all 14 Products in Family](#)

AI White LED Pattern Projector

See More by [Advanced Illumination](#)



Stock **#87-451** 1 In Stock

-

1

+

C\$1,085^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$1,085.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

SL191-WHIC	Model Number:
50,000	LED Lifetime (hours):

LED Illuminator	Type of Illumination:
-----------------	-----------------------

Note:
Optional Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are Available

Advanced Illumination	Manufacturer:
Spot Light	Geometry:
Constant	Illumination Mode:
Physical & Mechanical Properties	
20.8	Diameter of Compatible Reticle (mm):
Optical Properties	
White	Color:
Hardware & Interface Connectivity	
Flying Leads	Connector:
Power Supply: Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 233:

Product Details

- Multiple Wavelength Options Available
- Equip C-Mount [Imaging Lenses](#) to Control Illumination Geometry
- Ideal for 3D Reconstruction and Mapping

Advanced Illumination LED Pattern Projectors are compact illuminators designed for applications requiring structured illumination. These illuminators can be used with any C-mount compatible imaging lens and negatively patterned 21mm reticle to achieve specific structured illumination geometries. When used without a reticle, these illuminators can be adjustable spotlights. Advanced Illumination LED Pattern Projectors are ideal for 3D reconstruction and mapping. The illuminators are available in blue, green, red or white.

Note: [Power supply](#) and C-mount [imaging lens](#) are required and sold separately.</>

Technical Information



