

[All Products](#) / [Cameras](#) / [USB Cameras](#) / [Allied Vision Alvium Right Angle USB 3.1 Cameras](#)

[See all 127 Products in Family](#)

# Allied Vision Alvium 1800 U-500m, 1/2.5" 5.0MP CS-Mount, Right Angle USB 3.1 Monochrome Camera

See More by [Allied Vision](#)



Allied Vision Alvium Camera, Full Housing, CS-Mount, Right Angle IO Port (Front)

Stock **#14-136** [CONTACT US](#)

[Similar Cameras](#)

- 1 + **C\$441.00**

ADD TO CART

Qty 1+

C\$441.00

Volume Pricing

[Request Quote](#)

**Note:** This item requires accessories for use | [Learn More](#)

Get Product Downloads

**Video Output:**

USB 3.1 Gen 1

**Type:**

Monochrome Camera

**Manufacturer:**

|                                                                                             |
|---------------------------------------------------------------------------------------------|
| Allied Vision                                                                               |
| <b>Mounting Threads:</b><br>1/4-20 and M6 with Tripod Mount Adapter <a href="#">#14-156</a> |
| <b>Image Buffer:</b><br>256KB                                                               |
| <b>Camera Family:</b><br>Alvium Right Angle                                                 |
| <b>Model Number:</b><br>1800 U-500m                                                         |
| <b>Imaging Sensor:</b><br>ON Semi AR0521                                                    |
| <b>Type of Sensor:</b><br>Progressive Scan CMOS                                             |
| <b>Type of Shutter:</b><br>Rolling                                                          |
| <b>Camera Sensor Format:</b><br>1/2.5"                                                      |
| <b>Resolution (MegaPixels):</b><br>5.00                                                     |
| <b>Pixels (H x V):</b><br>2,592 x 1,944                                                     |
| <b>Pixel Size, H x V (µm):</b><br>2.2 x 2.2                                                 |
| <b>Sensing Area, H x V (mm):</b><br>5.7 x 4.3                                               |
| <b>Frame Rate (fps):</b><br>67.00                                                           |
| <b>Pixel Depth:</b><br>8/10 bit                                                             |
| <b>Exposure Time:</b><br>13µs - 849ms                                                       |
| <b>Connector:</b><br>USB 3.1 Gen 1, Micro-B                                                 |
| <b>Power Supply:</b><br>Power over USB or via GPIO                                          |
| <b>Power Consumption (W):</b><br>2.2                                                        |
| <b>GPIOs:</b><br>4 Programmable TTL GPIOs                                                   |
| <b>Synchronization:</b><br>Hardware Trigger (GPIO) or Software Trigger                      |
| <b>Dimensions (mm):</b><br>33 x 32 x 29 (includes connectors and lens mount)                |
| <b>Weight (g):</b><br>60                                                                    |
| <b>Mount:</b><br>CS-Mount                                                                   |
| <b>Housing:</b><br>Full                                                                     |
| <b>Interface Port Orientation:</b><br>Back Panel (Right Angle)                              |
| <b>Dynamic Range (dB):</b><br>63                                                            |
| <b>Operating Temperature (°C):</b><br>+5 to +65                                             |
| <b>Storage Temperature (°C):</b><br>-10 to +70                                              |
| <b>GPIO Connector Type:</b><br>7-pin JST                                                    |
| <b>Machine Vision Standard:</b><br>USB3 Vision v1.0, GenICam                                |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |